



BU-00000- *
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

CLIPS & INSULATORS

BU-30BL Miniature-Alligator with Barrel 5 Amp



[Enlarge](#)

- Full meshing teeth
- Rolled barrel tail section
- Steel
- Solder or crimp connection
- 3/16" (4.8mm) maximum jaw opening
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

BU-30TBO Miniature Alligator with Threaded Barrel - 5 Amp

- Steel with threaded steel barrel
- Connects to any 6-32 threaded male test prod
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)



[Enlarge](#)

BU-31 Insulator for BU-30BL or BU-30TBO

- Tough flexible vinyl
- Available in black, red, yellow, green, blue and white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

Alligator Clip with Barrel 10 Amp:

BU-60 (Steel)

BU-60C (Solid Copper)

BU-60X (Stainless Steel)

- Standard clip with barrel for a banana plug
- Solder or crimp connection
- 5/16" (7.9mm) max. jaw opening
- Nose width 0.13"
- Stainless steel clip, body, rivet and spring
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Insulated BNCs](#)|[Test Leads](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).