

[Search Engine](#) > Catalog: **TZ03R121E169B00**
[Capacitors](#) > [Ceramic Trimmer Capacitors](#)













## Specification

Global Part Number	TZ03R121E169B00
Previous Part Number	TZ03R121ER169
Cmin. (max.)	10.0pF
Cmax.	120.0pF +100/-0%
TC	N750±300ppm/°C
Q	300min. at 1MHz, Cmax.
Rated Voltage	50Vdc
Withstanding Voltage	110Vdc
Insulation Resistance (min.)	10000M ohm
Torque	2.0 to 15.0mNm
Operating Temperature Range	-25 to +85°C
Stator/Case Color	Black
Adjustment Direction	Top
Soldering Method	Flow
Height	4.8mm ±0.5
Weight	0.4g

## Minimum Quantity

180mm Paper Tape	
180mm Plastic Tape	
330mm Paper Tape	
330mm Plastic Tape	
Bulk Case	
Bulk(Bag)	1000
Ammo Pack	
320Reel	
Magazine	
Box	

## Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features\\_and\\_Applications](#)
-  [Temp.\\_Coeff.\\_Characteristics](#)
-  [Construction](#)
-  [Mounting\\_Holes](#)
-  [Notice\\_\(Storage\\_and\\_operating\\_condition\)](#)
-  [Temperature\\_Profile\(Flow\)](#)
-  [Notice\\_\(Soldering\\_and\\_mounting\)](#)
-  [Notice\\_\(Handling\)](#)
-  [Notice\\_\(Other\)](#)

**Product specifications in this catalog are as of May 2005,  
and are subject to change or obsolescence without notice.  
Please approve our product specifications or transact the approval sheet before ordering.  
Please read rating and !Cautions first.**

---

All products and company names herein are trademarks or registered trademarks of their respective owners.

---

[|TOP|](#)

All Rights Reserved, Copyright (c)  
**Murata Manufacturing Co., Ltd. 2005**