


# HBL1221I -- Industrial Series Switch




## Product Specifications

<p><b>Product Type</b></p>	 <p><b>Toggle Switches</b></p>
<p><b>Switch Type</b></p>	<p>Single Pole</p>
<p><b>Switch Handle Positions</b></p>	<p>2</p>
<p><b>Toggle Variety</b></p>	<p>Industrial</p>
<p><b>Amperage</b></p>	<p>20A</p>
<p><b>Voltage</b></p>	<p>120/277V AC</p>
<p><b>Color</b></p>	 <p><b>Ivory</b></p>

**Horsepower Conversion Table**

Amperage	120V AC	208V AC	240V AC	277V AC
15A	1/2 HP	1 1/2 HP	2 HP	2 HP
20A	1 HP	2 HP	2 HP	2 HP
<b>Listings</b>	UL Listed, CSA Certified			
<b>Fed Spec</b>	Verified to WS896			
<b>Base</b>	Thermoset, Color Coded by Amperage			
<b>Top</b>	Thermoset, Gray			
<b>Toggle</b>	Nylon			
<b>Terminals</b>	Brass			
<b>Terminal Screws</b>	Brass			
<b>Mounting Bridge</b>	Nickel Plated Steel			
<b>Contacts</b>	Silver Cadmium Oxide			
<b>Moveable Contact Arm</b>	Copper Alloy			
<b>Rocker</b>	Thermoplastic Elastomer			
<b>Ground Terminal</b>	Nickel Plated Steel			
<b>Ground Screw</b>	Brass			
<b>Auto Ground Clip</b>	Stainless Steel			
<b>Dielectric Voltage Withstand</b>	Withstands 1500V AC for 1 Minute			
<b>Max Working Voltage</b>	277V AC			
<b>Overload</b>	Minimum 4.8 times rated current for 100 cycles			
<b>Temperature Rise</b>	30° C maximum at rated current.			
<b>Max Continuous Current</b>	20A			
<b>Endurance</b>	50,000 cycles min. Tungsten Filament, Lamp Load Fed Spec #WS896, SP, DP, 3w & 4W			
<b>Terminal Accommodation</b>	#14 AWG Min - #10 AWG Max.			
<b>Flammability</b>	UL 94V-2			
<b>Operating Temperature</b>	Max Continuous: 75° C, Min Continuous: -40° C w/o Impact			
<b>Catalog Page</b>	<a href="#">Click here for catalog page C04</a>			
<b>M Drawings</b>	<a href="#">Click here for M-Drawing</a>			
<b>Brochures</b>	<a href="#">Click here for product brochure</a>			
<b>Hubbellnet</b>	<a href="#">Click here for Hubbellnet</a>			
<b>Catalog Section</b>	<a href="#">Click here for Section-C</a>			
<b>UPC Number</b>	78358543138			
<b>Weight in LBs</b>	0.2			

**SINGLE POLE**



Wiring Diagram

**Hubbell Incorporated (Delaware)**  
185 Plains Road  
Milford, CT 06460-2420  
Ph: (203) 882-4800  
Fax: (800) 255-1031



Wiring Device-Kellems