


HBL1223W -- Industrial Series Switch



Product Specifications


Product Type



Switch Type	Three Way
Switch Handle Positions	2
Toggle Variety	Industrial
Amperage	20A
Voltage	120/277V AC
Color	 White

Horsepower Conversion Table

Amperage	120V AC	208V AC	240V AC	277V AC
15A	1/2 HP	1 1/2 HP	2 HP	2 HP
20A	1 HP	2 HP	2 HP	2 HP
Listings	UL Listed, CSA Certified			
Fed Spec	Verified to WS896			
Base	Thermoset, Color Coded by Amperage			
Top	Thermoset, Gray			
Toggle	Nylon			
Terminals	Brass			
Terminal Screws	Brass			
Mounting Bridge	Nickel Plated Steel			
Contacts	Silver Cadmium Oxide			
Moveable Contact Arm	Copper Alloy			
Rocker	Thermoplastic Elastomer			
Ground Terminal	Nickel Plated Steel			
Ground Screw	Brass			
Auto Ground Clip	Stainless Steel			
Dielectric Voltage Withstand	Withstands 1500V AC for 1 Minute			
Max Working Voltage	277V AC			
Overload	Minimum 4.8 times rated current for 100 cycles			
Temperature Rise	30° C maximum at rated current.			
Max Continuous Current	20A			
Endurance	50,000 cycles min. Tungsten Filament, Lamp Load Fed Spec #WS896, SP, DP, 3w & 4W			
Terminal Accommodation	#14 AWG Min - #10 AWG Max.			
Flammability	UL 94V-2			
Operating Temperature	Max Continuous: 75° C, Min Continuous: -40° C w/o Impact			
Catalog Page	Click here for catalog page C04			
M Drawings	Click here for M-Drawing			
Brochures	Click here for product brochure			
Hubbellnet	Click here for Hubbellnet			
Catalog Section	Click here for Section-C			
UPC Number	78358543200			
Weight in LBs	0.2			



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031



Wiring Device-Kellems