

HBL2625 -- Twist-Lock Flanged Inlet



2P3W, 30A 250V, L6-30P, White Nylon

Product Specifications

Product Type



Product Item

Flanged Inlet

Wiring Scheme

2 Pole, 3 Wire Grounding

Amperage

30A

Voltage

250V AC

NEMA Configuration

L6-30P

Item Style

Standard

Device Color

White

Terminal Retainer Material

Clear polycarbonate

Blade Material

Brass

Terminal Clamp Material

.08" (2) steel-nickel plated


Terminal Screw Material

#10-32 Brass (white finish on neutral screw when used) Multi-drive

Ground Screw Material

#10-32 Brass (green finish) Multi-drive

Body Holding Screw Material	Steel, zinc plated Multi-drive
Body Contact Carrier Material	Natural White Nylon
Flanged Casing Material	Natural White Nylon
Mounting Screw Material	Nickel-plated Brass Round head screws
Ratings	Molded into face
Catalog No.	Permanently ink marked on casing
Dielectric Voltage Withstand	2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30 C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	30A #10 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	HB or better per UL 94 or CSA 22.2 No. 0.6
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Listings	UL/CSA
Catalog Page	Click here for catalog page B27
Brochures	Click here for product brochure
Hubbellnet	Click here for Hubbellnet
Catalog Section	Click here for Section-B
UPC Number	78358503889
Weight in LBs	0.2



Hubbell Incorporated (Delaware)
185 Plains Road
Milford, CT 06460-2420
Ph: (203) 882-4800
Fax: (800) 255-1031



Wiring Device-Kellems