

GEM-V FOOTSWITCH



Gem Footswitch

[Request A Quote](#)

Environmental Ratings:

EN 60529 Degree of Protection IP20

Key Benefits

Gem foot switch models feature a round black actuating cap in a chrome plated heavy die cast housing with a full nonskid base pad. Moderate pressure from any direction operates the foot switch. Standard models supplied with cordset are wired normally open and grounded.

Size: 3-13/16" x 1-7/32"

Weight: 1 lb.

SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)

▲ WARNING

	CATALOG NUMBER	DESCRIPTION	CIRCUIT	FORM	ELECTRICAL RATINGS
	GEM-V2	Momentary	SPDT	C	15 A 125-250 VAC 1/2 H.P. 125-250 VAC
	GEM-V3*	Momentary	SPST Wired N.O.	A	10 A 125 VAC 1/2 H.P. 125 VAC
	GEM-V36**	Momentary	SPST Wired N.O.	A	10 A 125-250 VAC 1/2 H.P. 125-250 VAC

*Supplied with 6 ft. 18/3 cord and 3 prong series plug. Green lead grounded. **Supplied with 6 ft. 18/3 cord without plug. Green lead grounded.