



FEATURES

- Compact Size
- Fast Fitting
- NO or NC by rotating 180 degrees
- 10W or 70W contacts
- Materials to suit most fluids
- Custom Designs Available
- UL approved (pending)

DESCRIPTION

The SRC Devices range of Vertical Liquid Level Sensors have been designed for use with many types of fluid to reliably indicate high or low levels depending on mounting position. They are manufactured with 10W or 70W (High Power) contacts and are easily mounted from inside the tank.


SPECIFICATIONS

Switching Voltage (V DC)	200
Switching Current (A)	0.5
Carry Current (A)	1.5
Contact Rating (VA)	10
Life Expectancy (Ops)	1 x 10 ⁹
Contact Resistance (Max, Ohms)	0.10
Contact Material	Ru
Insulation Resistance (Oh ms)	1 x 10 ¹¹
Operate Time (ms)	0.5
Release Time (ms)	0.2
Storage Temperature (°C)	-20 to +85°C
Shock Resistance (Gs)	30
Vibration Resistance (Gs)	20

MATERIAL INFORMATION

Material	Temperature Rating	Colour
POLYPROPYLENE	-20 to +85 °C	White
ABS	-20 to +85 °C	Red
PVDF	-20 to +90 °C	Black
PPS	-20 to +100 °C	Grey

MECHANICAL DIMENSIONS



ORDERING INFORMATION

